




PRESS-TO-MIX, Model 34524.

- Vigorous mixing action in testtubes.
- Mixing action starts upon depression of the rubber cup with the testtube.
- Continuous adjustable speed control allows for pre-set mixing speeds.
- Illuminated tumble switch for choosing Press-To-Mix mode or continuous mixing mode.
- Housing of enamelled steel.
- 4 Suction feet prevent 'creeping' of the apparatus on most surfaces, specially when it is running in the continuous mode.
- Supplied with line cord.
- Operation on 220 V, 50 Hz.
- Outer dimensions: 210 x 145 x 145 mm. (l. x w. x h.)
- Weight: 2 kg/ 4,4 lbs.



TEST-TUBE-ROTATOR, Model 34528.

- For mixing, diffusion, dialysing, etc.
- Housing of enamelled steel.
- A sparkless, synchronous, geared motor.
- Slow rotation speed, 10 rpm., permits tube exchange while operation.
- Can be set continuously at an angle between 90° and 270°.
- Three standard discs available with chemically resistant coated clamps to hold stoppered tubes, flasks or vials with body-or neckdiameters between 11 to 45 mm.
- The disc can be centered on the driving axis with a locking pin and a synthetic knob.
- Supplied with line cord but without disc.
- Operation on 220 V, 50 Hz.
- Outer dimensions: 200 x 200 x 205 mm. (l. x w. x h.)
- Weight: 4 kg / 8,8 lbs.



Accessories:

- 34002 Stainless Steel disc, ø 200 mm., with 20 clamps for tubes ø 11-15 mm.
- 34003 Ditto, with 20 clamps for tubes ø 14-18 mm.
- 34004 Ditto, with 10 clamps for tubes ø 37-45 mm.



DUAL PRESS-TO-MIX, Model 34525.

- A twin model in the same execution as Press-To-Mix, Model 34524.
- The mixing units are both fully independent and separately adjustable.
- Outer dimensions: 285 x 215 x 145 mm. (l. x w. x h.)
- Weight: 3,7 kg / 8,2 lbs.



ROCK 'N ROLLER, Model 34201.

- Keeps the contents of closed tubes in gentle motion by rocking while rolling.
- 14 Stainless Steel rotating bars, each: 208 x 10 mm. (l. x ø) with interspaces of 11 mm.
- Rolling speed: 10 rpm.
- Rocking frequency: 5 cycles/min. at 35° movement.
- An illuminated on/off switch.
- Supplied with line cord.
- Operation on 220 V, 50 Hz.

- Outer dimensions: 310 x 300 x 180 mm. (l. x w. x h.)
- Weight: 5 kg / 11 lbs.