

Hamilton™ Glass Syringes - Call for Pricing



Previous



Next

Table of Contents

Product Index

Search

Home

Contact Us



Previous



Next



800 Series Syringes

Syringe sizes from 5 to 250 µl available. Reinforced plunger. Replaceable plunger barrel assembly.

800 Series Syringes						
Catalog No.	Vol.	Ter.	Point Style	Ga.*	Replacement Needle (pkg. of 6)	Plunger Barrel Assembly
BS4 72-1724	5 µl	RN	2	26s	72-5744	BS4 72-1730
BS4 72-1725	10 µl	RN	2	26s	72-5744	BS4 72-1731
BS4 72-1726	25 µl	RN	2	22s	72-5745	BS4 72-1732
BS4 72-1727	50 µl	RN	2	22s	72-5745	BS4 72-1733
BS4 72-1728	100 µl	RN	2	22s	72-5745	BS4 72-1734
BS4 72-1729	250 µl	RN	2	22s	72-5746	BS4 72-1735



7000 Series Modified Microliter™ Syringes

Ultra low volume syringes: 0.5 to 5 µl. No Dead Volume – sample contained entirely in needle. Replaceable syringe barrels and parts. The KH repair kit includes KH needle, KH ferrule, plunger wire and instruction sheet.

7000 Series Modified Microliter™ Syringes					
Catalog No.	Volume	Terminus	Point Style	Gauge*	KH Repair Kit
BS4 72-1736	0.5 µl	KH	2	25	BS4 72-1749
BS4 72-1737	1 µl	KH	2	25s	BS4 72-1750
BS4 72-1738	1 µl	KH	2	22s	BS4 72-1751
BS4 72-1739	2 µl	KH	2	25	BS4 72-1752
BS4 72-1740	2 µl	KH	2	23	BS4 72-1753
BS4 72-1741	5 µl	KH	2	24	BS4 72-1754
BS4 72-1742	0.5 µl	KH	3	32	BS4 72-1755
BS4 72-1743	0.5 µl	KH	3	25	BS4 72-1756
BS4 72-1744	1 µl	KH	3	25s	BS4 72-1757
BS4 72-1745	1 µl	KH	3	22s	BS4 72-1758
BS4 72-1746	2 µl	KH	3	25	BS4 72-1759
BS4 72-1747	2 µl	KH	3	23	BS4 72-1760
BS4 72-1748	5 µl	KH	3	24	BS4 72-1761

* Note: An 's' after the gauge size refers to a special needle size, see chart on page A72.



1700 Series GASTIGHT® Syringes

Teflon® PTFE tipped plungers. Replaceable plungers and needles. Sizes: 10 to 500 µl. Replacement needles are sold in packages of 3.

1700 Series GASTIGHT® Syringes (pkg. 6)							
Catalog No.	Vol.	Ter.	Point Style	Ga.*	Replacement Parts Needle	Plunger	Barrel
BS4 72-1762	10 µl	LT	-	-	-	BS4 72-1785	-
BS4 72-1763	25 µl	LT	-	-	-	BS4 72-1786	-
BS4 72-1764	50 µl	LT	-	-	-	BS4 72-1787	-
BS4 72-1765	100 µl	LT	-	-	-	BS4 72-1788	-
BS4 72-1766	250 µl	LT	-	-	-	BS4 72-1789	-
BS4 72-1767	500 µl	LT	-	-	-	BS4 72-1790	-
BS4 72-1824	5 µl	RN	3	32	BS4 72-5743	Call	-
BS4 72-1825	10 µl	RN	3	32	BS4 72-5743	BS4 72-1785	-
BS4 72-1768	10 µl	RN	2	26s	BS4 72-5744	BS4 72-1785	-
BS4 72-1769	25 µl	RN	2	22s	BS4 72-5745	BS4 72-1786	-
BS4 72-1770	50 µl	RN	2	22s	BS4 72-5745	BS4 72-1792	-
BS4 72-1771	100 µl	RN	2	22s	BS4 72-5745	BS4 72-1793	-
BS4 72-1772	250 µl	RN	2	22s	BS4 72-5746	BS4 72-1794	-
BS4 72-1773	500 µl	RN	2	22	BS4 72-5747	BS4 72-1795	-
BS4 72-1774	10 µl	RN	3	22s	72-5751	BS4 72-1785	-
BS4 72-1775	25 µl	RN	3	22s	BS4 72-5751	BS4 72-1786	-
BS4 72-1776	50 µl	RN	3	22s	BS4 72-5751	BS4 72-1792	-
BS4 72-1777	100 µl	RN	3	22s	BS4 72-5751	BS4 72-1793	-
BS4 72-1778	250 µl	RN	3	22s	72-5753	BS4 72-1794	-
BS4 72-1779	500 µl	RN	3	22	BS4 72-5752	BS4 72-1795	-
BS4 72-1781	50 µl	TLL	-	-	-	BS4 72-1792	BS4 72-1797
BS4 72-1782	100 µl	TLL	-	-	-	BS4 72-1793	BS4 72-1798
BS4 72-1783	250 µl	TLL	-	-	-	BS4 72-1794	BS4 72-1799
BS4 72-1784	500 µl	TLL	-	-	-	BS4 72-1795	BS4 72-1800
BS4 72-1780	25 µl	TLLX	-	-	-	BS4 72-1791	BS4 72-1796
BS4 72-1901	50 µl	TLLX	-	-	-	BS4 72-1808	BS4 72-1897
BS4 72-1902	100 µl	TLLX	-	-	-	BS4 72-1809	BS4 72-1798
BS4 72-1903	250 µl	TLLX	-	-	-	BS4 72-1810	BS4 72-1799
BS4 72-1904	500 µl	TLLX	-	-	-	BS4 72-1811	BS4 72-1800
BS4 72-1801	10 µl	CX	¼-28	-	-	BS4 72-1807	BS4 72-1905
BS4 72-1802	25 µl	CX	¼-28	-	-	BS4 72-1791	BS4 72-1906
BS4 72-1803	50 µl	CX	¼-28	-	-	BS4 72-1808	BS4 72-1907
BS4 72-1804	100 µl	CX	¼-28	-	-	BS4 72-1809	BS4 72-1908
BS4 72-1805	250 µl	CX	¼-28	-	-	BS4 72-1810	BS4 72-1909
BS4 72-1806	500 µl	CX	¼-28	-	-	BS4 72-1811	BS4 72-1910

Connect With Us

