




NTB-1B



NTB-2B

## 变倍体视显微镜 ZOOM STEREO MICROSCOPE

### MODEL NTB-1B

观察物体成正立体像,图像清晰,分辨率高  
 镜体 360° 可转  
 连续变倍比 4:1  
 电源 110V 或 220V 任选  
 透射 / 落射卤素灯照明(两档选择)  
 荧光灯落射照明可供选择,220V 或 110V/8W  
 附件: 0.5X、0.75X 附加物镜,16X 目镜

### FEATURE:

Up-right and Sharp Image with High Resolution  
 Main Body 360° Rotatable  
 Zoom Ratio 4:1  
 Power Supply 110V or 220V  
 Transmitted/Incident Halogen Lamp  
 Circular Fluorescent Lamp 220V or 110V/8W as Optional Accessory  
 Optional Accessories: Objectives 0.5X, 0.75X and Eyepiece 16X

物镜 Objective	变倍物镜 Zoom Objective	附 2X 物镜 With 2X Objective
Eyepiece	1X-4X	2X-8X
10X	10X-40X	20X-80X
20X	20X-80X	40X-160X
工作距离 Working Distance	97MM	30MM

### 型号 MODEL NTB-2B

### 性能:

- 被观察物体成正立体像,图像清晰,分辨率高
- 镜体 360° 可转
- 连续变倍比 4:1
- 电源 110V 或 220V 任选
- 透射 / 落射卤素灯照明(两档选择),透射 12V/12W,落射 12V/15W
- 可增加透射 / 落射卤素灯同时照明,透射 12V/12W,落射 12V/15W
- 环形荧光灯落射照明可供选择,220V 或 110V/8W
- 可供附件:0.5X,1.5X,2X 附加物镜,5X,15X,20X 目镜

### FEATURE:

-Up-right and Sharp Image with High Resolution  
 -Main Body 360° Rotatable  
 -Zoom Ratio 4:1  
 -Power Supply 110V or 220V  
 -Transmitted/Incident Halogen Lamp, Transmitted 12V/12W, Incident 12V/15W  
 -The Function of Transmitted and Incident Light at Same Time may be Added.  
 -Circular Fluorescent Lamp 220V or 110V/8W as Optional Accessory  
 -Optional Accessories: Objectives 0.5X,1.5X,2X and Eyepiece 5X,15X,20X

物镜 Objective	变倍物镜 Zoom Objective
目镜 Eyepiece	1X-4X
10X	10X-40X
工作距离 Working Distance	90MM