

## the automatic shoe cover dispenser

Eliminate Cross Contamination
No More Accidents or Back Injury
Saves Time and Cost Effective
Quick and Easy Application in Seconds



# easyshu revolutionises the application of shoe covers

The **easyshu** range of sanitary shoe cover dispensers offers you a rapid, hygenic and safe system for the protection of sensitive environments from contamination.

Each easy to use, easy to maintain station allows users to quickly cover their footwear without the need to bend while balancing on one foot during application.

easyshu is the ideal solution for a large range of environments including pharmaceutical companies, hospitals, laboratories, food processing, medical and as well as the petrochemical, engineering and construction industries.



STEP 1 Place foot into pre-opened cover



**STEP 2** Press lightly downward with little effort



**STEP 3** Remove foot complete with fitted cover

# shuon2000

#### Automatic Shoe Cover Dispenser

Dimensions:	70x37x90cm
Power Supply:	220V
,	50/60Hz
<b>Operation Supply:</b>	12Vdc
Consumption:	50W
Weight:	20kg

## shuon720

#### **Manual Shoe Cover Dispenser**

**Dimensions: Power Supply:** Weight: Capacity:

76x34.5x99cm Manual 20kg **100 Covers** 

# shuoff1100

#### Automatic Shoe Cover Remover

**Dimensions: Power Supply: Operation Supply: 12Vdc** Consumption: **50W** Weight:

70x37x90cm 220V 50/60Hz

### 20kg

# shuon302

New and Innovative, Handy Portable Shoe Cover Dispenser **Dimensions:** 70x37x90cm







the automatic shoe cover dispenser



### EASY-TO-USE

Allows users to quickly cover footwear without touching shoe covers.



### SAFE

Reduces the risk of accidents and back injury - no need to bend down to fit shoe covers.



### HYGENIC

Removes the need to place hands near unclean footwear.



### **COST EFFECTIVE**

Hugely reuces the time taken to apply and remove shoe covers.



### SHOE COVER MATERIAL

CPE - 2g, 3g, 4g, 5g (blue or white), PE, Non-Woven.



### EASY TO RELOAD

Simply open the cover and insert the cartridge in the receptacle provided. Then, just close the cover and press the 'SET' button to count out the covers used.

Holds 1 Cartridge Loaded and 2 Cartridges in the cavity (600 in total).



# the automatic shoe cover dispenser





Connect With Us f y 🖸 😥 💶 🔞 🚥

